



Torque screwdriver with 1/4 inch bit holder, with scale, automatic triggering, maximum torque: 600cNm



Order data

| | |
|--------------|---------------|
| Order number | 659985 600 |
| GTIN | 4000896260065 |
| Item class | 630 |

Description

Version:

- **Very easy to read thanks to large, clear numeric display.**
- **Short 36° release distance with clearly audible signal.**
- **Bit holder (1/4 inch – D 6.3 / F 6.3) with quick release fastener – fast bit changes with one hand.**
- **“Ratchet function” with free-running mechanism, reversible and can be locked, enables fast working due to smooth re-gripping action when tightening/loosening screw connections, even in confined spaces**
- **Release mechanism made of high-alloy tool steel – wear resistant.**
- **Overload clutch (“Slipper”) ensures the set value is not exceeded.**
- **Lock symbols clearly indicate the locking status.**

Units of measurement: cNm/Nm

Accuracy: +/- 6%

Standard:

Geprüft nach **DIN EN ISO 6789**.

Technical description

| | |
|-------------------|------------------------|
| Trigger principle | mechanical slip clutch |
|-------------------|------------------------|

| | |
|----------------------------------|------------------------------------|
| Setting the trigger value | with adjustment scale |
| Measurement process | Torque |
| Torque measuring accuracy | ±6 % |
| Reversible reading | Nm |
| Reversible reading | cNm |
| maximum torque | 600 cNm |
| Feedback | triggering |
| Direction of tightening | For right and left-hand tightening |
| Display | analogue |
| Scale graduation, 1 graduation = | 10 cNm |
| Torque range | 100 - 600 cNm |
| Overall length L | 198 mm |
| Torque range | 1 - 6 Nm |
| Measurement technology | mechanical |
| Connection format | Bit holder 1/4 inch |
| Bit socket | D 6.3 |
| Bit socket | F 6.3 |
| Adjustable trigger value | adjustable |
| Data can be recorded | no |
| Calibration | O3 |
| Release signalling | haptic |
| Test certificate | Manufacturer's test certificate |
| Standard | DIN EN ISO 6789 |
| Torque fixed setting | no |
| Type of product | Torque screwdriver |

Services

DAkkS calibration Torque wrench clockwise / anti-clockwise maximum torque 1000/2 N·m

020040 1000/2

020260 0,04-20/2

CalibrationTorque screwdrivers, clockwise / anti-clockwise
maximum torque 0,04-20/2 N·m
