


DC.T 11T308, Grade: KW10

Order data

| | |
|--------------|---------------|
| Order number | 260492 KW10 |
| GTIN | 4960664359776 |
| Item class | 25E |

Description

DC.T 11T308 KW10 Grade: KW10

Chip breaker: AH

Tolerance: G

Cutting depth a_p : 0.5 - 3 mm

Feed f : 0.05 - 0.25 mm/rev.

Cutting speed v_c main application: 30 - 300 m/min

Technical description

| | |
|--------------------------------------|---------------------|
| Chip breaker | AH |
| Cutting depth a_p | 0.5 - 3 mm |
| Cutting speed v_c main application | 30 - 300 m/min |
| Main application | N |
| Corner radius | 0.8 mm |
| Cutting conditions | continuous |
| Feed f | 0.05 - 0.25 mm/rev. |

| | |
|-------------------------------|------------------------------|
| Grade | KW10 |
| Finishing/roughing assignment | Semi-roughing |
| Tool material | Carbide |
| ISO code indexable insert | DCGT 11T308 |
| Number of changes/inserts | 2 |
| Tolerance | G |
| Type of product | Indexable insert for turning |