



Torque screwdriver with 1/4 inch bit holder, with scale, automatic triggering, maximum torque: 120cNm



Order data

Order number	659985 120
GTIN	4000896260041
Item class	630

Description

Version:

- **Very easy to read thanks to large, clear numeric display.**
- **Short 36° release distance with clearly audible signal.**
- **Bit holder (1/4 inch – D 6.3 / F 6.3) with quick release fastener – fast bit changes with one hand.**
- **“Ratchet function” with free-running mechanism, reversible and can be locked, enables fast working due to smooth re-gripping action when tightening/loosening screw connections, even in confined spaces**
- **Release mechanism made of high-alloy tool steel – wear resistant.**
- **Overload clutch (“Slipper”) ensures the set value is not exceeded.**
- **Lock symbols clearly indicate the locking status.**

Units of measurement: cNm/Nm

Accuracy: +/- 6%

Standard:

Geprüft nach **DIN EN ISO 6789.**

Technical description

Test certificate	Manufacturer’s test certificate
Torque measuring accuracy	±6 %
Measurement technology	mechanical
Reversible reading	Nm
Reversible reading	cNm

Adjustable trigger value	adjustable
Connection format	Bit holder 1/4 inch
Standard	DIN EN ISO 6789
Display	analogue
Release signalling	haptic
Trigger principle	mechanical slip clutch
Overall length L	196 mm
Torque range	0.2 - 1.2 Nm
Feedback	triggering
Setting the trigger value	with adjustment scale
Calibration	O1
Torque range	20 - 120 cNm
Scale graduation, 1 graduation =	1 cNm
Bit socket	D 6.3
Bit socket	F 6.3
Direction of tightening	For right and left-hand tightening
Measurement process	Torque
Data can be recorded	no
Torque fixed setting	no
Type of product	Torque screwdriver

Services

CalibrationTorque screwdrivers, clockwise / anti-clockwise maximum torque 0,04-20/2 N·m	020260 0,04-20/2
---	------------------