



KOMET KUB Quatron® indexable drill Combination shank, 2×D, Ø DC m7: 19mm



Order data

Order number	235500 19
GTIN	
Item class	24P

Description

Version:

With combination shank.

- Optimised coolant channels for reliable chip evacuation.
- Point angle 174° for almost flat-bottomed holes.

Application:

- For stationary and rotating use.
- For difficult drilling conditions (rolling scale, sloping surfaces of castings, interrupted cutting).
- For bores with tolerance ± 0.2 mm.

With indexable inserts No. 236520 – 236576.

Supplied with:

Clamp screws (without indexable inserts).

Note:

Further sizes available on request.

Technical description

Number of cutting edges Z	1
Reach L ₁	38 mm
Pack of insert screws	239652 6IP2 (1.0 Nm)
ISO code indexable insert	SOEX 060306 18-..
Shank Ø D _s	25 mm
Shank length L _s	56 mm

Series	KUB Quatron®
Nominal Ø D	19
for inch Ø	3/4 in
Overall length L	118 mm
Overhang L _A	62 mm
Drill depth for indexable insert drill up to	2×D
Shank	DIN 6535 HE, DIN 6595
Use for drilling	Centre drilling
Use for drilling	limited cross-drilling
Use for drilling	oblique spot drilling
Use for drilling	Cross-drilling
Use for drilling	Centre drilling
Use for drilling	Aperture
Use for drilling	oblique exit
Use for drilling	convex
Through-coolant	yes
Type of product	Indexable drill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 6IP	674252 6IP
Torque screwdriver, fixed setting set torque 1,0 N·m	211750 1,0
Torx Plus® insert screw set 10 pieces Drive 6IP2	239652 6IP2