

Garant**Eco clamping toolholder PCLNL 95°, for indexable inserts CN., left-hand****Order data**

Order number	250013 20/12
GTIN	4045197649812
Item class	21U

Description**Version:**

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

Technical description

ISO code toolholder	PCLNR/L 2020X12
Spring	259046 1
suitable indexable insert	CN.. 1204..
Lever screw	259018 2
Head length L ₁	34 mm
Functional width L ₄	25 mm
Shank size	20 mm
Insert size	12 mm
Lever	259015 3

Data sheet

Shim	259031 11
Overall length L	93 mm
Series	Eco
Application type	left-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250013-20/12>