


VNGA 160404, PT600M, Application range: GG

Order data

Order number	255856 GG
GTIN	4960664546664
Item class	25F

Description
Version:

MEGACOAT coated ceramic inserts.

Grade: PT600M

Chamfer: T02025

Cutting depth a_p : 0.5 - 2.5 mm

Feed f : 0.15 - 0.4 mm/rev.

Cutting speed v_c main application: 150 - 550 m/min

Technical description

Corner radius	0.4 mm
Feed f	0.15 - 0.4 mm/rev.
Cutting conditions	continuous
Cutting conditions	heavily interrupted
Cutting conditions	slightly interrupted
Application range	GG

Cutting depth a_p	0.5 - 2.5 mm
Cutting speed v_c main application	150 - 550 m/min
Chamfer	T02025
Grade	PT600M
Finishing/roughing assignment	Semi-roughing
Tool material	Ceramic
ISO code indexable insert	VNGA 160404
Number of changes/inserts	4
Product name attribute	PT600M
Type of product	Indexable insert for turning