

Garant
QuickTurn clamping toolholder, left-hand, Shank / insert size: 20/12mm

Order data

Order number	250015 20/12
GTIN	4045197649850
Item class	21U

Description
Application:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce ancillary times.

Through-coolant: no

ISO code toolholder: DCLNR/L 2025K12

suitable indexable insert: CN.. 1204..

Functional width L_4 : 32 mm

Head length L_1 : 32 mm

Overall length L: 125 mm

Shim: 259031 3

Technical description

Head length L_1	32 mm
suitable indexable insert	CN.. 1204..
Functional width L_4	32 mm
ISO code toolholder	DCLNR/L 2025K12
Shim	259031 3
Clamp	259038 7
Shim screw	259025 4

Shank size	20 mm
Insert size	12 mm
Overall length L	125 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim	259201
Shim Type 3	259031 3
Clamping claw	259351
Clamping claw Type 7	259038 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Clamping claw	259531
Clamping claw Type 11	259038 11
Shim screw Type 4	259025 4
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Shim screw	259171