

MIRKA**Random orbital sanders DEROS II, Type: 625****Order data**

Order number	077335 625
GTIN	6416868231274
Item class	07E

Description**Version:**

Random orbital sander with **brushless electric motor without a power supply unit.**

- **Low power consumption. Especially compact, quiet, lightweight and powerful.**
- **20% more powerful motor than DEROS I, maintains constant speed under heavy load.**
- **WLAN connectivity and enhanced Bluetooth connectivity.**
- **RPM LED indicator on the speed controller + on/off button and lockable speed.**
- **Can be connected to an external extraction system.**

Application:

Material removal work (coarse, intermediate, and fine abrasion) for wood, metal, and paint. Ideally suited for abrasive surfaces that are difficult to access or profiled, working wet or dry.

Note:

Suitable grinding disc 6-hole article No. 567775, 15-hole article No. 567558 and ABRANET article No. 567800.

Suitable backing pad article No. 567990 size 150.

Technical description

Power supply	Mains-powered
Backing pad Ø	150 mm
maximum vibration to EN	< 2,5 m/s ²

Speed of oscillation	4000 - 10000 min ⁻¹
Interface	Bluetooth interface
Series	DEROS II
Weight	1 kg
Orbital stroke	2.5 mm
Power consumption	400 W
Type of product	Random orbital sanders

Accessories

Multi-hole PU backing pad External Ø 150 mm	567990 150
---	------------