

**Mitutoyo****Linear scale, effective measuring length L0: 350mm**

## Order data

Order number	499241 350
GTIN	4550501371483
Item class	44D

## Description

**Version:**

- **With absolute measuring system.**
- **After switching on, the current position is displayed; thus it is not necessary to move to reference points.**
- **Straightforward assembly and installation.**
- **Resistant to water, oil, and dust due to electromagnetic induction.**

**Function:**

IP67: Protected against intermittent immersion in water and protected against penetration by dust (dust-tight), also completely protected against touching.

**Application:**

For exact measurement and positioning of axial adjustments e.g. on milling machines, lathes, positioning tables or measurement tools. Also suitable for converting machine tools to digital display.

**Note:**

**Applicable only in conjunction with display unit No. 499356.**

## Technical description

IP Index of Protection	IP 67
Overall length L <sub>3</sub>	538 mm
Power supply	Mains-powered
Measuring accuracy (20°)	5 µm

effective measuring length $L_0$	350 mm
Width	22 mm
Cable length	3.5 m
Hole centre distance $L_2$	518 mm
maximum micrometer head distance $L_1$	380 mm
Measured value saving	Once-off setting of the zero position
Measurement technology	digital
Type of product	Linear scale

---

## Accessories

Digital display Number of displayed axes 2	499356 2
Digital display Number of displayed axes 3	499356 3