

Garant
QuickTurn clamping toolholder, left-hand, Shank / insert size: 25/12mm

Order data

Order number	250015 25/12
GTIN	4045197649867
Item class	21U

Description
Application:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce ancillary times.

Through-coolant: no

ISO code toolholder: DCLNR/L 2525M12

suitable indexable insert: CN.. 1204..

Functional width L₄: 32 mm

Head length L₁: 32 mm

Overall length L: 150 mm

Shim: 259031 3

Technical description

ISO code toolholder	DCLNR/L 2525M12
Shank size	25 mm
Shim screw	259025 4
Shim	259031 3
Insert size	12 mm
Functional width L ₄	32 mm
suitable indexable insert	CN.. 1204..

Clamp	259038 7
Head length L ₁	32 mm
Overall length L	150 mm
Series	QuickTurn
Application type	left-hand
Standard	DIN ISO 5610
Through-coolant	no
Setting angle κ	95 °
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Clamping claw	259531
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
Shim Type 3	259031 3
Clamping claw Type 11	259038 11
Shim screw Type 4	259025 4
Shim screw	259171
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Clamping claw Type 7	259038 7
Clamping claw	259351
Shim	259201