

Garant

eco lever lock toolholder, short, right-hand, Shank / insert size: 25/12 mm


Order data

Order number	250012 25/12
GTIN	4045197648396
Item class	21U

Description
Version:

With internal coolant feed right to the cutting edge. Cooling by means of precision nozzles effectively and efficiently reduces the thermal loading, since the coolant stream is optimally directed between the chip and cutting edge. This results in higher productivity, longer tool life and greater process reliability.

Note:

Coolant transfer only possible in conjunction with GARANT eco system toolholders No. 319001 – 319886 or for shank length < 125 mm plus No. 317900.

Through-coolant: yes

ISO code toolholder: PCLNR/L 2525X12

suitable indexable insert: CN.. 1204..

Functional width L_4 : 32 mm

Head length L_1 : 34 mm

Overall length L: 105.5 mm

Shim: 259031 11

Technical description

Insert size	12 mm
Lever screw	259018 2
Lever	259015 3
suitable indexable insert	CN.. 1204..
Shim	259031 11

Spring	259046 1
Functional width L ₄	32 mm
Head length L ₁	34 mm
ISO code toolholder	PCLNR/L 2525X12
Shank size	25 mm
Overall length L	105.5 mm
Application type	right-hand
Standard	DIN ISO 5610
Through-coolant	yes
Setting angle κ	95 °
Type of product	Boring bar

Accessories

Lever Type 3	259015 3
Shim Type 11	259031 11
Spring Type 1	259046 1
Lever screw Type 2	259018 2