



Cordless circular saw, Type: M12FCS442



Order data

Order number	078207 M12FCS442
GTIN	4058546483609
Item class	03L

Description

Version:

M12 FUEL™ cordless circular saw with brushless POWERSTATE™ motor.

- **Magnesium shoe reduces the weight and maximises the service life.**
- **Built-in dust blower keeps the cutting line clear.**
- **LED light illuminates the cutting line for better visibility.**

Note:

See from No. 073814 and No. 073839 for suitable spare batteries and starter kits.

Technical description

Weight	7.8 kg
Version	Hand-held circular saw
maximum cutting depth 90°	44 mm
Power supply	Mains operated
Number of rechargeable batteries contained	2
Manufacturer's designation	M12 FCS442 502X
Type of rechargeable battery	Lithium-ion
Saw blade bore Ø	20 mm

Battery capacity	5 Ah
Packaging	Modular case (HD=Heavy Duty)
maximum vibration to EN	1.5 m/s ²
maximum speed	3600 min ⁻¹
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V
Saw blade Ø	140 mm
Battery voltage	12 V
Type of product	Saw

Accessories

Li-ion system M12B4 Battery type MB12	073815 MB12
Li-ion system M12B6 Battery type MB12	073829 MB12
Battery charger Type M1218C	073840 M1218C
Battery charger Type M1218FC	073840 M1218FC
Battery charger Type M1218SC	073840 M1218SC