

JEPSON POWER**Metal cutting hand-held circular saw, Type: 8203****Order data**

Order number	078234 8203
GTIN	4260052466797
Item class	07E

Description**Version:**

Powerful metal cutting cold circular saws for sawing sheet metal, sandwich panels, metal plates, tubes and sections of steel, non-ferrous metals, and composite materials **without generating sparks.**

- **No need to use cooling lubricants.**
- **No reworking necessary.**
- **Cuts in seconds.**

Metal cutting **hand-held circular saw.**

- **Precise blade guidance, low burr formation.**
- **Sturdy stop plate.**

Metal-cutting **hand-held circular saw.**

- **Depth adjustment with scale.**
- **Chip compartment.**
- **Suitable for metal sheets up to 10 mm as well as sandwich panels and profiles up to 67 mm.**

Note:

Slides for 078234 available on request:

Slide 1400 mm for size 8320

Slide 600-1200mm for size 8230.

Metal cutting circular saw DRY MITER Cutter 9410ND for delicate sawing in soft and delicate material available on request. The metal-cutting hand-held circular saw is available as a cordless version under No. 078234 size 8203E.

Technical description

Power supply	Mains-powered
Weight	6.3 kg
Power consumption	1700 W
Saw blade Ø	203 mm
AC supply voltage	230 V
maximum speed	3700 min ⁻¹
Manufacturer's designation	8203
maximum cutting depth 90°	67 mm
Mains frequency	50 Hz
maximum cutting depth 45°	42 mm
Packaging	Transport case
Type of product	Saw