



Carbide-tipped hammer drill set "MX4", Number of drills: 5



Order data

Order number	789062 5
GTIN	4058546521660
Item class	76G

Description

Version:

Drill head with square cross-section. Increased drilling speed due to 4-cutter head. Double the service life compared to 2 cutters. Large-volume 4-flute design. TARGET TIP TECHNOLOGY - tip angled more acutely:

more precision when drilling, no slipping along the surface, more aggressive in rebar and greater drilling speed.

PGM certified – verified precise and wall-plug-capable drill holes, both for chemical and for physical anchors.

PACKOUT-compatible plastic case.

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort. Very smooth action, perfect for truly circular holes. **4-flute** design for quick clearance of waste material, low vibration, and high stability. Less tiring for the operator and less load on the machine.

Content:

Hammer drill No. 789050: 1 pc. each

Size 5; 6 length 115 mm;

Size 6; 8; 10 length 165 mm

Technical description

Number of cutting edges Z	5
Packaging	Plastic case
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill