



LED inspection lamp with battery, Lamp head Ø: 15mm



Order data

Order number	081421 15
GTIN	2050001894885
Item class	08C

Description

Version:

Exceptionally robust inspection lamps made from **solid aluminium** with LED lamp head. Battery grip including flexible neck, splash-proof. 1 pc. stainless steel inspection mirror 40x65 mm unbreakable, 1 pc. inspection mirror Ø 30 mm, screw-on ring magnet.

Technical description

Illumination	25 lm
Battery type	LR6
Article no of the battery / rechargeable battery fitted	081559 LR6
ATEX zone	no
Overall length	560 mm
Head Ø	15 mm
Number of batteries contained	2
Power supply	Battery-powered

Spread angle	10 degrees
Type of product	Inspection lamp

Accessories

Magnetic base	081413
Alkaline-manganese batteries International size LR6	081561 LR6
Mirror set for LED inspection lamp / workshop lamp set2 pieces	081427
Button cell / special battery Battery type SL760	081560 SL760