

Garant
GARANT Master TM plain shank thread mill 2×D, AlTiN, UNC: 7/16-14

Order data

Order number	139732 7/16-14
GTIN	4067263129004
Item class	11D

Description
Version:

Solid carbide thread milling cutters **with irregular cutting edge spacing and an increased number of cutting edges**. Due to the **irregular cutting edge spacing** they achieve very **smooth running** and **long tool life**.

Newly developed universal geometry and **high-performance coating** for use across a wide spectrum of materials.

- **Significantly reduced vibration due to irregular cutting edge spacing.**
- **Increased number of cutting edges.**
- **The latest generation of AlTiN-based HiPIMS coating.**
- **Corrected thread profile for avoidance of profile distortions.**

Application:

For **UNC unified coarse threads** ASME-B1.1.

Note:

HB and HE shanks are available at the same price as HA

Order **HB** shank: with **No. 139732 + 129100 HB**

Order **HE** shank: with **No. 139732 + 129100 HE**

Technical description

Number of clamping slots	6
Thread size	7/16-14 UNC
Thread type	UNC-LH
Thread type	UNC
Flute length L_c	22.6 mm

No. of teeth Z	6
Threads per inch	14
Nominal $\varnothing D_c$	7.95 mm
Feed f_z in steel $< 750 \text{ N/mm}^2$	0.08 mm
Overall length L	70 mm
Thread pitch	1.814 mm
Thread \varnothing	11.11 mm
Shank length L_s	36 mm
Shank $\varnothing D_s$	8 mm
Series	Master TM
Coating	AlTiN
Flank angle	60 degrees
Tool material	Solid carbide
Shank	DIN 6535 HA to h6
Through-coolant	yes
Cutting direction	right-hand
Application for type of drilling	up to $2 \times D$ for through holes
Application for type of drilling	up to $2 \times D$ for blind holes
Spacing of the cutters	unequal spacing
Shank tolerance	h6
Colour ring	green
Internal/external application	Internal
Type of product	thread milling cutter

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	220 m/min	N
Aluminium (short chipping)	suitable	220 m/min	N

Alu > 10% Si	suitable	180 m/min	N
Steel < 500 N/mm ²	suitable	140 m/min	P
Steel < 750 N/mm ²	suitable	130 m/min	P
Steel < 900 N/mm ²	suitable	120 m/min	P
Steel < 1100 N/mm ²	suitable	90 m/min	P
Steel < 1400 N/mm ²	suitable	80 m/min	P
Steel < 50 HRC	suitable only under restricted conditions	45 m/min	H
TOOLOX 33	suitable	85 m/min	H
TOOLOX 44	suitable	50 m/min	H
INOX < 900 N/mm ²	suitable	82 m/min	M
INOX > 900 N/mm ²	suitable	75 m/min	M
Ti > 850 N/mm ²	suitable	50 m/min	S
GG(G)	suitable	120 m/min	K
CuZn	suitable	200 m/min	N
Uni	suitable		
wet maximum	suitable		
wet minimum	suitable		
Air	suitable		

Services

Shank grinding Type HB	129100 HB
Shank grinding Type HE	129100 HE