

Labelling machine, Type: LM640CB



Order data

Order number	085500 LM640CB
GTIN	3026982021045
Item class	08U

Description

Version:

Robust portable labelling machines for fast and simple production of self-adhesive plastic labels. Permanent thermal transfer printing. Adjustable tape advance and reverse. Power supply from rechargeable Li-ion battery, mains charger. Simple text generation with quick-access buttons. Labelling made easy on the go. Advanced, compact and versatile labelling device. The LabelManager Executive 640 CB is suitable for both D1 standard and high-performance lettering tapes with widths from 6 mm to 24 mm, available in a variety of colours and designs. Experience the convenience of labelling on the go with the LabelManager Executive 640 CB. Designed for professionals on the move, the rechargeable lithium-ion battery and compact design make it easy to create labels wherever you are. The textured handle offers comfort even during prolonged use and reflects our commitment to excellent ergonomics. With its high-resolution screen for unsurpassed readability and intuitive and clear menu navigation, the LabelManager Executive 640 CB sets a new standard for label creation and customisation. In addition, the LabelManager Executive 640 CB's ease of use and dual connectivity options, such as Bluetooth Low Energy technology and USB-C, allow virtually unlimited* personalised labels to be stored via DYMO mobile and desktop software applications, promoting streamlined workflows and eliminating the need to connect the device. Whether you are organising your workplace or are in the field, the LabelManager Executive 640 CB gives you unparalleled efficiency and precision in labelling tasks. The device is compatible with D1 standard and high-performance lettering tapes with a width between 6 mm and 24 mm. Easy mobility with rechargeable lithium-

ion battery.Space-saving design with compact dimensions and textured surface for ergonomic grip.Large, high-resolution colour screen (240×320 pixels) for unparalleled readability.Dual connectivity via USB-C and Bluetooth Low Energy technology, eliminating the need to connect devices.Virtually unlimited* storage capacity for labels via the DYMO LabelManager Executive Connect app and DYMO Connect for Desktop software.Direct access to the DYMO LabelManager Executive Connect app and DYMO Connect for Desktop software.Direct compatibility with multiple devices (PC, Mac, smartphone and tablet) and operating systems (Android/iOS). With full-colour touch screen, also prints graphics, barcodes and logos with 300 dpi resolution. USB-C interface and Bluetooth.

Feature:

Date and time, serialisation (automatic numbering), barcode (EAN13, EAN8, UPC-A, UPC-E, CODE 128B, CODE 39), automatic shut-down, vertical printing, mirror printing, preview, WYSIWYG display, zoom, QR code via connected software. Font styles:Normal, bold, italic, outline, shadow, bold+italic and their combinations with underline. Font sizes:8pt, 10pt, 12pt, 16pt, 20pt, 24pt, 32pt, 40pt, 46pt. Max print lines: 5 Printing system: Thermal transfer. Resolution: 180 dpi Languages: Czech, Danish, German, Estonian, English, Spanish, French, Italian, Latvian, Lithuanian, Hungarian, Dutch, Norwegian, Polish, Portuguese, Romanian, Slovak, Finnish, Swedish, Turkish

Application:

The labels stick to nearly all smooth grease-free surfaces.

Supplied with:

Includes lettering tape black on white and user instructions. LabelManager labelling device1 pc. D1 standard lettering taperechargeable batteryUSB-C cable (USB-C to USB-C)Quick guide

Note:

Different language versions can be installed.With German QWERTZ keyboard ex stock, French AZERTY keyboard available on a short lead time.

Technical description

Number of text lines	5
Number of lettering styles	12
Type of rechargeable battery	Lithium-ion
Power supply	Mains operated
Manufacturer's designation	LabelManager™ Executive 640 CB
Height	75 mm
Width	150 mm
Special features	Bluetooth
Special features	USB-C
Length	185 mm

Data sheet

Tape cut-off type	automatic
Keyboard layout	QWERTZ
Number of font sizes	9
suitable tape cartridge	D1
available tape widths	6 to 24 mm
Weight including rechargeable battery	695 g
Type of product	Labelling machine