

 KOMET

**KOMET Reamax® TS holder Plain shank, short, for reaming head Ø D:  
27-34,99mm**

**Order data**

Order number	239880 27-34,99
GTIN	4047109230453
Item class	27E

**Description**
**Suitable for :**

Reaming heads No. 239805; 239811; 239816; 239822; 239826.

**Supplied with:**

Holder complete with pull stud, spanner for pull stud and activation key.

Please order a hexagon key L-wrench separately if required.

Through-coolant: yes

Overhang A: 120 mm

Overall length  $L_{tot}$ : 176 mm

Shank length  $L_s$ : 56 mm

Shank Ø  $D_s$  h6: 25 mm

Pull stud No. 239900: 4

Wrench No. 239901: 8AF

**Technical description**

Pull stud No. 239900	4
Overhang A	120 mm
Shank length $L_s$	56 mm
for reaming head Ø D	27 - 34.99 mm
Activation wrench No. 239902	3AF (5Nm)
Overall length $L_{tot}$	176 mm
Wrench No. 239901	8AF

Shank $\varnothing$ D <sub>s</sub> h6	25 mm
Shank type	short
Through-coolant	yes
Type of product	Phillips bit

---

## Accessories

Wrench for pull studs Drive SW8	239901 SW8
Pull stud Type 4	239900 4