


HOLEX
**HOLEX Pro Steel high-precision countersink with unequal spacing 90°, TiAlN,
External Ø Dc: 6,3mm**

Order data

Order number	GG1582 6,3
GTIN	4067263133155
Item class	GGN

Description
Version:
Same as No. 150182
All countersinks have 3 cutting edges, radially relieved.

Flutes are ground from solid.

- **Exact machining results in manual and machine use.**
- **Chatter-free running through extremely unequal spacing of the cutting edges for high-quality surfaces.**
- **Optimum tool life thanks to TiAlN high-performance coating.**
- **High process reliability due to optimised chip evacuation.**
- **Attractive cost/benefit ratio.**

Application:

High-precision countersink for chatter-free 90° countersinking.

Technical description

Shank tolerance	h9
Feed f in steel < 500 N/mm ²	0.09 mm/rev.
Overall length L	45 mm
Number of cutting edges Z	3

smallest countersink \varnothing for holes from	1.5 mm
Shank $\varnothing D_s$	5 mm
for countersunk screws DIN 7991	M3
External \varnothing	6.3 mm
Coating	TiAlN
Countersink tip angle	90 degrees
Tool material	HSS
Spacing of the countersink cutting edges	unequal spacing
Standard	DIN 335 C
Shank	Plain shank with h9
Through-coolant	no
Colour ring	green
Series	Pro Steel
Type of product	Stepped drill and countersink

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	75 m/min	N
Aluminium (short chipping)	suitable	70 m/min	N
Steel < 750 N/mm ²	suitable	50 m/min	P
Steel < 900 N/mm ²	suitable	40 m/min	P
Steel < 1100 N/mm ²	suitable	20 m/min	P
Steel < 1400 N/mm ²	suitable	15 m/min	P
Steel < 55 HRC	suitable only under restricted conditions	8 m/min	H
INOX < 900 N/mm ²	suitable	18 m/min	M
INOX > 900 N/mm ²	suitable	15 m/min	M
Ti > 850 N/mm ²	suitable only under restricted conditions	12 m/min	S

GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		

Accessories

HOLEX Pro Steel high-precision countersink with unequal spacing 90° External Ø Dc 6,3 mm

150182 6,3