


Garant**Machine tap, vaporised, M: M4****Order data**

Order number	GG5451 M4
GTIN	4067263135289
Item class	GGN

Description**Version:****Same as No. 135450.**Particularly sturdy design. **HSS-E****Technical description**

Number of clamping slots	3
Shank square <input type="checkbox"/>	3.4 mm
Tolerance class	ISO 2 6H
Thread \varnothing	4 mm
Shank $\varnothing D_s$	4.5 mm
Tool material	HSS E
Thread depth	8 mm
Overall length L	63 mm
Tapping hole \varnothing	3.3 mm
Number of cutting edges Z	3
Thread size	M4

Standard	DIN 371
Thread pitch	0.7 mm
Thread type	M
Coating	vaporised
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 2×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	blue
Type of product	Taps

User data

	Suitability	V _c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	13 m/min	N
Steel < 500 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 750 N/mm ²	suitable only under restricted conditions	15 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	15 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	13 m/min	N
Oil	suitable		

wet maximum

suitable only under
restricted conditions

Accessories

Machine tap M M4

135450 M4

Machine tap6G M M4

135600 M4