

HOLEX**TMSERROR, Fleece structure: 220/5****Order data**

| | |
|--------------|---------------|
| Order number | GG5115 220/5 |
| GTIN | 4067263136101 |
| Item class | GGN |

Description**Version:**

Synthetic nylon fleece impregnated with abrasive grit in synthetic resin bonding. Contains no materials that could cause corrosion, for wet and dry use (**similar to 556110; 556115**). similar to 556115.

Advantage:

- **Adapts to the component shape.**
- **The open structure prevents clogging and reduces heat development.**
- **Even and reproducible finish.**
- **Can be used wet or dry.**
- **Contains no materials that could cause corrosion.**

Application:

Can be used by hand, on hand block No. 556020 or on an orbital sander.

Content:

5 rolls / bulk pack.

Note:

Only sold in bulk pack quantities, not supplied individually. Ordering information: 1 set = 1 bulk pack.

Technical description

| | |
|---|-------------------------|
| Iron, sulphur and chlorine constituents | < 0.1 % |
| Roller width | 115 mm |
| Roll length | 10 m |
| Product name attribute | 115 mm × 10 m |
| Type of product | Roll of abrasive fleece |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable | | |
| CuZn | suitable | | |
| Plastic, GRP | suitable | | |
| Wood | suitable | | |
| Stone | suitable only under restricted conditions | | |
| Paint | suitable | | |
| Uni | suitable | | |
| wet maximum | suitable only under restricted conditions | | |
| dry | suitable | | |

Accessories

Roll of abrasive fleece Fleece structure 220

556115 220