

Garant GRIDLINE

Pull-out frame for hanging goods 200 kg, 36×24G, Type: 90**Order data**

Order number	998264 90
GTIN	4067263136057
Item class	91R

Description**Version:**

Pull-out frame with **100% full extension and differential runners**. Open in front, shell height at sides 46 mm, installation height 100 mm. With 5 cross tubes. Aluminium handle with labelling strips that can be exchanged and rewritten. With one-handed individual drawer release system.

Suitable for:

Drawer/shelf combination units, container equipment.

Supplied with:

Pull-out frame each complete with 1 pair drawer runner rails.

Colour:

RAL 7035 light grey **powder-coated**.

Note:

Not compatible with tool cabinets from group 93, can only be installed in drawer/shelf combination units.

Technical description

Application range	Container equipment
Drawer usable area in G	36×24
Weight	40 kg
Installation height	90 mm
Individual drawer release system	One-hand
Usable depth in G	24
Usable width in G	36

Total load capacity	200 kg
Drawer/pull-out shelf load capacity	200 kg
Drawer runner extension (partial/full extension)	100
Height adjustment interval	25 mm
Colour selection	RAL 9002, 7035, 7005, 7016, 6011, 5018, 5012, 5011, 5005, 3003
Product name attribute	36×24G
Usable width	900 mm
Usable depth	600 mm
Type of product	Pull-out shelf