

**GARANT Vap Tap machine tap HSS-E Form C, vaporised, M: M3****Order data**

Order number	135805 M3
GTIN	4069515002202
Item class	13V

Description**Version:****Form C** (2–3 turns lead chamfer).**Form C** (2–3 turns lead chamfer).**Technical description**

Thread pitch	0.5 mm
Standard	DIN 371
Thread size	M3
Thread type	M
Thread depth	9 mm
Number of clamping slots	3
Shank square □	2.7 mm
Shank Ø D _s	3.5 mm
Overall length L	56 mm
Tolerance class	ISO 2 6H
Thread Ø	3 mm
Number of cutting edges Z	3
Tapping hole Ø	2.5 mm
Tool material	HSS E

Data sheet

Coating	vaporised
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	C
Helix angle	40 degrees
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for blind holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Vap Tap
Type of product	Taps

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	18 m/min	N
Aluminium (short chipping)	suitable	13 m/min	N
Steel < 500 N/mm ²	suitable	18 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		

