

**GARANT Vap Tap machine tap left-hand thread HSS-E 6H, vaporised, M-LH: M8****Order data**

Order number	132802 M8
GTIN	4069515001946
Item class	13V

Description**Version:**

GARANT Vap Tap universal tap – left-hand thread can be used reliably in a wide range of materials. Optimised **neck and flute length** for **improved chip evacuation** when working on **deep** threads. High-performance **HSS-E tool material** with higher vanadium content for improved **wear resistance**. **Surface vaporised** for reduced edge build-up.

Technical description

Thread depth	24 mm
Tool material	HSS E
Thread Ø	8 mm
Tapping hole Ø	6.8 mm
Thread type	M-LH
Shank Ø D _s	8 mm
Number of clamping slots	3
Thread size	M8
Number of cutting edges Z	3
Thread pitch	1.25 mm
Overall length L	90 mm
Tolerance class	ISO 2 6H

Data sheet

Shank square ☐	6.2 mm
Standard	DIN 371
Coating	vaporised
Flank angle	60 degrees
Thread standard	DIN 13
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	left-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Series	Vap Tap
Type of product	Taps

User data

	Suitability	V _c	ISO code
Alu plastics	suitable	18 m/min	N
Aluminium (short chipping)	suitable	13 m/min	N
Steel < 500 N/mm ²	suitable	18 m/min	P
Steel < 750 N/mm ²	suitable	15 m/min	P
Steel < 900 N/mm ²	suitable	15 m/min	P
Steel < 1100 N/mm ²	suitable	6 m/min	P
INOX < 900 N/mm ²	suitable	6 m/min	M
CuZn	suitable only under restricted conditions	15 m/min	N
Uni	suitable		
Oil	suitable		

wet maximum	suitable
-------------	----------