

Garant
Nut lock 2GP90, Contents: 50ml

Order data

Order number	GG8063 50
GTIN	4067263136446
Item class	00N

Description
Version:

The use of thread-lockers prevents the screw fastenings from accidentally releasing and coming undone. The single-component anaerobic thread-lockers are suitable for all thread types and forms. Screw fastenings are sealed. Seizing is reliably prevented.

Type **2GP90** medium-strength. Reliable sealing of cast housings and weld seams. Also for subsequently securing and fixing small screws and cylindrical parts.

Feature:

Contents: 3 pieces

Application:

Low strength – Can be undone with normal tools. **Medium strength** – Can be undone with normal tools. **High strength** – Can be undone only with special tools or by heating (>150°C).

Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

Technical description

Operating temperature range	-55 - 180 °C
Dynamic viscosity	10 - 20 mPas

Density	1.08 g/cm ³
Colour	green
Working life after date of manufacture	24 mo
Suitable for material	Metal
Sustainability	GARANT GreenPlus
minimum break-away torque	10 - 15 Nm
Flashpoint	100 °C
Touch dry after	40 - 60 min
Storage temperature	5 - 23 °C
Series	GreenPlus
Shape	liquid
Characteristics	sealing
Characteristics	fluorescent under UV light
Suitable for application area	general purpose use
Suitable for application area	Nut lock
Suitable for application area	pre-assembled screw fastenings
Suitable for application area	Thread sealing
Chemical basis	Methacrylate
Capacity	50 ml
for thread size M to	M6
Strength class	medium strength
Functional strength to	5 - 8 h
Type of product	Nut lock

Accessories

Thread locking2GP90 Contents 50 ml	088063 50
------------------------------------	-----------