

Garant**Thread sealant 5GP11, Contents: 50ml****Order data**

Order number	GG8065 50
GTIN	4067263136460
Item class	00N

Description**Version:**

Thread sealants prevent leakage of gaseous and liquid media. Thread sealants are typically used for sealing conical metal threads and connecting pieces, amongst other things.

Type **5GP11**. Seals against water, compressed air, gas, petrol, LPG, and chemical products.

Thixotropic. PTFE additive allows easy disassembly. Specially for sealing conical/cylindrical pipe screw connections. When it has cured it creates an elastic coating.

Feature:

Contents: 3 pieces

Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

Technical description

Dynamic viscosity	15000 - 25000 mPas
Disassembly	with normal tool
Chemical basis	Methacrylate ester
minimum break-away torque	5 - 15 Nm

Strength class	low strength
for imperial thread size	3 in
Operating temperature range	-55 - 180 °C
Shape	liquid
Suitable for material	Metal
Functional strength to	1 - 3 h
Sustainability	GARANT GreenPlus
Flashpoint	100 °C
Working life after date of manufacture	24 mo
Capacity	50 ml
Series	GreenPlus
for thread size M to	M80
Suitable for application area	Pipe sealant
Suitable for application area	Screw fastenings
Suitable for application area	Pipe threads
Touch dry after	15 - 20 min
Colour	white
Density	1.09 g/cm ³
Storage temperature	5 - 23 °C
Type of product	Sealant

Accessories

Thread sealant5GP11 Contents 50 ml	088065 50
------------------------------------	-----------