

Garant**Joint connection 6GP38, Contents: 50ml****Order data**

Order number	GG8069 50
GTIN	4067263137306
Item class	00N

Description**Version:**

When using joining as a production technique, two or more components are connected through positive contact. When using the adhesive, the full jointing face is used to establish a solid connection. It allows for high force transfer and dynamic loads (high shear strength).

Type **6GP38**. Quick-curing universal product with very high strength for static shear stresses and dynamic loads. For fixing gears, pulleys, rotor/shaft connections on electric motors.

Feature:

Contents: 3 pieces

Note:

Clean the material to be worked on in advance with cleaner without hazard labels No. 088004.

Technical description

Functional strength to	1 - 3 h
Storage temperature	5 - 23 °C
Chemical basis	Methacrylate
Sustainability	GARANT GreenPlus

Capacity	50 ml
Maximum gap size	0.25 mm
Dynamic viscosity	3000 - 6000 mPas
Flashpoint	100 °C
Series	GreenPlus
Characteristics	hardens quickly
Characteristics	fluorescent under UV light
Touch dry after	5 - 15 min
Density	1.09 g/cm ³
Suitable for application area	Thread sealing
Suitable for application area	Joint connection
for thread size M to	M36
Shape	liquid
Suitable for material	Metal
minimum break-away torque	40 Nm
Working life after date of manufacture	24 mo
Colour	green
Strength class	high-strength
Operating temperature range	-55 - 180 °C
Type of product	Jointing product

Accessories

Joint connection6GP38 Contents 50 ml

088069 50