



Grinding disc CC-GRIND#View SGP STEELOX, Type: 125mm



Order data

Order number	566363 125
GTIN	4007220494189
Item class	550

Description

Version:

Aggressive grinding disc with **integral glass fibre pad**.

Application:

For **hard and rough grinding work** on surfaces and edges.

Cost-effective alternative to rough grinding discs with **significantly reduced heat stress, noise, dust, and vibration**.

Note the flat working angle and powerful drive (>1200 W).

Material:

Machinable materials:

Case-hardened steels

Stainless steel (INOX)

Steel

Tool steels

wood

Technical description

Disc Ø	125 mm
Bore Ø	22.23 mm

Grinding medium code	Ceramic
Iron, sulphur and chlorine constituents	< 0,1 %
optimised for material	INOX
recommended approach angle	5-15 degrees
maximum circumferential speed	80 m/s
Number of positions	1
Type of product	Grinding disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable only under restricted conditions		
dry	suitable		