


Garant

Electronic torque analyser, maximum torque: 2N·m



Order data

Order number	654413 2
GTIN	4067263138341
Item class	61D

Description

Version:

For use of mechanical and digital branded torque wrenches (not HCT) and screwdrivers, and setting and checking triggering, indicating, right-hand and left-hand turning torque wrenches and screwdrivers.

- **Display:** Large sharp contrast illuminated 2.8 inch TFT display with double scale with viewing angle stability. With memory capacity display.
- **Memory capacity:** 1000 measurement values with time stamp (incl. date and time) and 20 configurable test cases.
- **Modes:** Tracking display (Track), trigger point sensing (First-Peak) and peak value display (Peak Hold).
- **Attachment:** can be attached to flat surfaces (table, wall, etc.) using 4 screws (M10).
- **3 recesses** for secure storage of adapters (increaser piece).
- **Data output:** Available via USB-C. The data can be exported as a .csv file.
- **Password protection:** available as protection against unauthorised access to the menu (master password) and for verifying test cases. In addition, you can set that reworking a test case that has been performed incorrectly requires input of a password.
- **Warning signals:** visual (change of colour on the display) and acoustic (buzzer). The pre-warning point can be configured individually. The acoustic warning signal can be disabled if desired.
- **Protection class** IP40

- **Languages: German, English, Spanish, Italian, French.**
- **Factory settings: Can be reset to the factory settings.**
- **Displays the software version with the serial number and date of the last calibration. The date of the next calibration can be set on the torque analyser.**

Units of measurement: Nm, lbfft, lbfin.

Function:

IP40: Protected against penetration by foreign bodies with $\varnothing > 1$ mm, however tools and wires should be kept away, and offers no protection against water.

Accuracy:

Clockwise and anti-clockwise: $\pm 1\%$.

Supplied with:

USB-C data cable (1.8 m), power supply unit, country adapter (types A, C, G and I), certificate of conformity. Supplied in a sturdy plastic case. Adapter 1/4 inch square to 1/4 inch hexagon C 6.3 (similar to No. 676950 size 4/4).

Note:

Suitable additional adapters can be found under No. 649550 and No. 650006.

Technical description

Power supply	Mains-powered
maximum torque	2 Nm
Weight	2.8 kg
Square socket	1/4 in
Display unit depth	161 mm
Display unit width	146 mm
IP Index of Protection	IP 40
Torque measuring accuracy	$\pm 1\%$
Display unit height	86 mm
Measuring range	0.1 - 2 Nm
Resolution	0.01 Nm
Direction of tightening	For right and left-hand tightening
Interface	USB interface
Test certificate	Manufacturer's test certificate
Calibration	O4
Type of product	Torque analyser

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/654413-2>
