


**KOMET® M03Speed micro-adjustable drilling head, Ø Dmin: 62mm**

**Order data**

Order number	238370 62
GTIN	4047109081574
Item class	24I

**Description**
**Version:**

- **Dynamic balance in the slide for highest speeds.**
- **Modular system structure.**
- **Fine adjustment without additional clamping.**
- **With ABS® connection for highest changeover accuracy.**
- **Quick rough adjustment by adjusting the lathe tool.**
- **Internal coolant supply directed to the cutting edge.**
- **Smallest adjustment steps in the µm range, within a fine adjustment range of 0.25 - 0.6 mm on the Ø, depending on the turning range.**
- **Fine adjustment steps of 0.002 mm per graduation in Ø.**
- **High resolution ensures problem-free adjustment / readability without a vernier.**

**Application:**

In combination with replaceable bridge No. 238372.

**Note:**

Additional insert holders, e.g. for reverse machining and with other angles = 15°, 30°, 45° etc. available on short lead times.

Please order change-over adapters, cartridges, and indexable inserts separately.

**Technical description**

maximum speed	18500 min <sup>-1</sup>
Fine adjustment in Ø	0.6 mm

Cutter circle Ø D2 forwards machining	55 mm
Minimum Ø D <sub>min</sub>	62
ABS® shank Ø D <sub>s</sub>	50
Blade carrier	238374 62-82
Change-over adapter	238372 62; 82
Boring range Ø	62 - 103 mm
Shank	ABS
Use for drilling	Cross-drilling
Use for drilling	convex
Use for drilling	oblique exit
Through-coolant	yes
Type of product	Boring tool

## Accessories

KOMET® cartridge 90° for M03SpeedForwards suitable for M03 Size 62-82

238374 62-82