

Garant
QuickTurn clamping toolholder, right-hand, Shank / insert size: 20/12mm

Order data

| | |
|--------------|---------------|
| Order number | 250014 20/12 |
| GTIN | 4045197649836 |
| Item class | 21U |

Description
Application:

Inserts can be changed without using tools. **Release the stop at the push of a button – change the insert – press the clamp to secure it.**

A simple and convenient way to reduce ancillary times.

Through-coolant: no

ISO code toolholder: DCLNR/L 2025K12

suitable indexable insert: CN.. 1204..

Functional width L₄: 32 mm

Head length L₁: 32 mm

Overall length L: 125 mm

Shim: 259031 3

Technical description

| | |
|----------------------------|-----------------|
| suitable indexable insert | CN.. 1204.. |
| ISO code toolholder | DCLNR/L 2025K12 |
| Shank size | 20 mm |
| Head length L ₁ | 32 mm |
| Insert size | 12 mm |
| Shim | 259031 3 |
| Clamp | 259038 7 |

| | |
|---------------------------------|-------------------------------|
| Shim screw | 259025 4 |
| Functional width L ₄ | 32 mm |
| Overall length L | 125 mm |
| Series | QuickTurn |
| Application type | right-hand |
| Standard | DIN ISO 5610 |
| Through-coolant | no |
| Setting angle κ | 95 ° |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Clamping claw | 259351 |
| Shim | 259201 |
| Shim screw Type 4 | 259025 4 |
| Shim screw | 259171 |
| Shim Type 3 | 259031 3 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |
| Clamping claw Type 7 | 259038 7 |
| Clamping claw | 259531 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659906 500 |
| Clamping claw Type 11 | 259038 11 |