

**Front-gripper grip wrench, overall length: 125mm****Order data**

Order number	708310 125
GTIN	4069515040778
Item class	72B

Description**Version:**

Serrated jaws and sturdy spring steel body. Span and clamping pressure adjustable with a knurled screw. Fully nickel-plated. Handle with multi-component covering.

Application:

For gripping, tightening and loosening screw heads and bolts, as well as for clamping profiled and flat materials.

1. Use the knurled screw to adjust the gripping jaws to the screw head.
2. Tighten the adjustment screw another 90 – 180° clockwise.
3. Push the handles to lock the jaws. Turn and loosen the screw.

Material:

Jaws of high-quality steel, hardened and tempered

Note:

Spare springs No. 708301 sizes 5CJ and 8.5CJ.

Technical description

Jaw capacity	26 mm
overall length	125 mm
Jaw length (serrated area)	20 mm
Clamping width for screw head Ø	3 - 9.5 mm
Type of product	Grip wrench

