



Pro Eco lever lock toolholder PCLNR 95°, for indexable inserts PC., right



Order data

Order number	250044 20/12
GTIN	4069515004008
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Overall length L	125 mm
Insert size	12 mm
Shank size	20 mm
Standard	Works standard
Functional width L ₄	31 mm
suitable indexable insert	CN.. 1204..
ISO code toolholder	PCLNR/L 2020K12
Shim	259034 1
Lever	259016 1
Lever screw	259019 1
Head length L ₁	26 mm
Series	Pro Eco

Pin	259045 1
Application type	right-hand
Through-coolant	yes
Setting angle κ	95 degrees
Application	Facing
Application	External longitudinal turning
Type of product	Screw-on toolholder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250044-20/12>