



Pro Eco lever lock toolholder DDJNR 93°, for indexable inserts DD., right



Order data

Order number	250632 25/15
GTIN	4069515004039
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Lever	259016 1
suitable indexable insert	DN.. 1506..
Insert size	15 mm
ISO code toolholder	PDJNR/L 2525M15
Overall length L	150 mm
Functional width L ₄	32 mm
Shank size	25 mm
Shim	259034 2
Lever screw	259019 2
Standard	Works standard
Head length L ₁	36 mm
Pin	259045 1

Application type	right-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250632-25/15>