



Pro Eco lever lock toolholder DDJNL 93°, for indexable inserts DD.., left



Order data

Order number	250633 20/15
GTIN	4069515004084
Item class	22E

Description

Version:

Targeted cooling on the cutting edge.

Note:

Coolant transfer under the head via hose connection (G1/8 inch – included in delivery).

Technical description

Head length L ₁	36 mm
Functional width L ₄	32 mm
Standard	Works standard
Lever	259016 1
ISO code toolholder	PDJNR/L 2020K15
Insert size	15 mm
Shim	259034 2
Shank size	20 mm
suitable indexable insert	DN.. 1506..
Lever screw	259019 2
Overall length L	125 mm
Pin	259045 1

Application type	left-hand
Through-coolant	yes
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	Facing
Type of product	Screw-on toolholder

Suitable products

<https://www.hoffmann-group.com/GB/en/hom/p/250633-20/15>