

**BMT boring bar holder, BMT: 68****Order data**

Order number	319887 68
GTIN	4069515004640
Item class	32U

Description**Version:**

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

For internal and external cooling.

Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball injection nozzles up to 80 bar.**

Application:

Internal and external machining in CNC lathes with BMT tool turrets.

For internal machining with boring bar holder or indexable drills.

Suitable for:

CNC lathes with BMT tool turret.

- **Mazak: QT/QTS 100 M/MY/MS/MSY; QT/QTS 200, 250 M/MY/MS/MSY; QT 200, 250 M/MY/MS/MSY (16D); QTC/QTE/QTU 100-350 M/MY/MS/MSY; QT-Ez 8, 10, 12 M/MY/MSY; MZ68B/C**

Note:

Other BMT holders with different sizes and dimensions are available on request.

Please note that you must check the compatibility of the holder with your machine before purchasing. We cannot guarantee that it will fit correctly.

Technical description

L_3	26 mm
L_2	110 mm
l_1	132 mm
d_a	40 mm
L_1	68 mm
Z	64 mm
x	95 mm
h_1	85 mm
Type of product	Steel toolholder