



## BMT boring bar holder, BMT: 65-72



### Order data

|              |               |
|--------------|---------------|
| Order number | 319887 65-72  |
| GTIN         | 4069515004671 |
| Item class   | 32U           |

### Description

#### Version:

High-precision arbors adapted to the specific machine, for flexible use on main and counter-spindle machines. Contact face and functional face ground. Perfectly matched for the respective lathe.

For internal and external cooling.

#### Advantage:

- **Design optimised for weight and geometry.**
- **Process reliability thanks to high-quality materials, long working life.**
- **Burnished for better corrosion protection.**
- **With secured ball injection nozzles up to 80 bar.**

#### Application:

Internal and external machining in CNC lathes with BMT tool turrets.

For internal machining with boring bar holder or indexable drills.

#### Suitable for:

CNC lathes with BMT tool turret.

- **ACCUWAY: UT-300**
- **DMC: DL 35; DL 40**
- **DN SOLUTIONS (formerly DOOSAN): PUMA DNT 2100; PUMA DNT 2600; Puma 300 MS; PUMA V400 M; PUMA VT450 M**

- **ECOCA:** MT-3; MT-4
- **FOCUS CNC:** FBL-300
- **GANESH:** ASL-15; ASL-78/105
- **HAAS:** ST-35; ST-28; DS-30; ST-20; ST-25; ST-30
- **HARDINGE:** ELITE 65 M Ultra
- **HEADMAN:** T65
- **HURCO:** TMX10; TMX8
- **HWACHEON:** CUTEX 240; HI-TECH 230S; HI-TECH 350; HI-TECH 450; HI-TECH 200; VT 450; HI-TECH 230
- **HYUNDAI WIA:** L2100
- **JOHNFORD:** SL-60; SL-65
- **LEADWELL:** LTC-25
- **LMW:** LR30
- **SMART:** NL 2500; NL 3000
- **SMEC:** SL 2500; PL 2000; PL 2500; PL 2000; PL 2500; SLV 500; PL 20; PL 25; PL 35; SL 3500; SL 3000
- **SPINNER:** TC800
- **Tongtai:** TCS-1500; TCS-2000; TCS-2500

## Note:

Other BMT holders with different sizes and dimensions are available on request.

Please note that you must check the compatibility of the holder with your machine before purchasing. We cannot guarantee that it will fit correctly.

## Technical description

|                 |                  |
|-----------------|------------------|
| L <sub>2</sub>  | 70 mm            |
| l <sub>1</sub>  | 105 mm           |
| h <sub>1</sub>  | 95 mm            |
| Z               | 64 mm            |
| d <sub>a</sub>  | 40 mm            |
| x               | 72 mm            |
| L <sub>3</sub>  | 51 mm            |
| L <sub>1</sub>  | 73 mm            |
| Type of product | Steel toolholder |