

magnetoplan®

Magnetic flip chart writing board, for flexible height adjustment**Order data**

Order number	974541 M
GTIN	4013695021720
Item class	930

Description**Version:**

The mobile flipchart for convenient working and high quality standards. The solid, robust all-steel design ensures it is very sturdy. Pleasant to use thanks to the ring-shaped base with foot recess. With 5 lockable castors. Simple, stepless height adjustment using compression spring system and locking screw. Magnetic, powder-coated metal surface. Can be written on with board markers; dry-erase surface. Complete with 2 insertable side arms (magnetic), for 3 times the presentation area. Elegant, rounded clamp and adjustable attachment pins. For all commercially available blocks of paper. Full-length storage tray for markers and accessories (accessories such as flipchart paper are not included in delivery).

Colour:

White / light grey.

Technical description

Board for magnetic clamps	yes
Storage tray available	yes
Footprint depth	650 mm

Data sheet

Board for writing on	yes
Material of the surface	Metal
height-adjustable	yes
Type	Mobile
Number of wheels	5
Installation situation	Round base with 5 castors
Material of foot	Steel
Weight	16 kg
Height	1950 mm
with set of pens	no
Height adjustment range	1540 - 1950 mm
Footprint width	650 mm
Board height	950 mm
Board width	680 mm
Type of product	Flipchart