

**Cordless dust extraction system, Manufacturer's designation: M12DE****Order data**

Order number	070226 M12DE
GTIN	4002395002740
Item class	03L

Description**Version:**

General-purpose compact lightweight **battery-extraction system** for hammer drills with clamping neck Ø from 43 to 59 mm.

- **HEPA filter traps 99.97 % of all dust particles.**
- **Lockable depth stop with 120 mm scale**
- **REDLINK™ electronics.**
- **Switch settings: On, off, automatic with 5 seconds run-on time for complete extraction.**
- **Can be attached to either the right side or left side of the drill.**
- **Red Li-ion batteries with single-cell monitoring and charge display.**

Supplied with:

Supplied with 1× 12 V / 2.0 Ah Red Li-ion battery, charger. HD box (modular case), additional handle, spare suction spigots, 3 adapters to match the clamping neck Ø.

Attention:

German version. Order free UK adapter plug No. 08 1172_GB.

Note:

See No. 073814 / 3815 / 3816 and No. 073840 for suitable spare batteries and chargers.

The manufacturer's warranty conditions can be found on page 1470.

Packaging: Modular case (HD=Heavy Duty)

suitable battery - supplier / battery type / voltage: Milwaukee type B 12 V

Battery voltage: 12 V

Battery capacity: 2 A·h

Weight: 1.7 kg

Technical description

Battery voltage	12 V
Manufacturer's designation	M12DE
Weight	1.7 kg
Battery capacity	2 A·h
Packaging	Modular case (HD=Heavy Duty)
suitable battery - supplier / battery type / voltage	Milwaukee type B 12 V

Accessories

Li-ion system M12B4 Rechargeable battery type, battery voltage MB12 V	073815 MB12
Battery charger Manufacturer ID M1218C	073840 M1218C
Battery charger Manufacturer ID M1218FC	073840 M1218FC