



## Knurl forming tool Sliding headstock lathe universal, Shank size: 16mm



### Order data

|              |           |
|--------------|-----------|
| Order number | 290089 16 |
| GTIN         |           |
| Item class   | 29H       |

### Description

#### Version:

Grub screws in the shank for clearance angle correction.

Carbide roller pin for increased wear resistance.

**Modular design: Can be used universally as right-hand or left-hand version.**

### Technical description

|  |                             |
|--|-----------------------------|
| Working range                            | 3 - 40 mm                   |
| for knurl width w                        | 6 mm                        |
| for knurled countersunk Ø d <sub>3</sub> | 11 mm                       |
| for knurl bore Ø d <sub>2</sub>          | 6 mm                        |
| Closure stud                             | 299925 1                    |
| for knurl Ø d <sub>1</sub>               | 15 mm                       |
| Disc                                     | 299927 1                    |
| Cutting direction                        | left-hand and right-hand    |
| for knurl profile                        | RAA 2×AA                    |
| Type of product                          | Self-centring knurling tool |