



## Cut knurling tool Sliding headstock lathe universal, Shank size: 10mm



### Order data

|              |           |
|--------------|-----------|
| Order number | 290198 10 |
| GTIN         |           |
| Item class   | 29H       |

### Description

#### Version:

**Modular design: Can be used universally as right-hand or left-hand version.**

Carbide running sleeve for increased wear resistance.

Quick tool adjustment by using the adjustment spindle.

Grub screw in the shank for clearance angle correction.

### Technical description

|                                   |                          |
|-----------------------------------|--------------------------|
| for knurl $\varnothing d_1$       | 15 mm                    |
| Carbide sleeve, cover disc, screw | 299920 11                |
| for knurl bore $\varnothing d_2$  | 8 mm                     |
| for knurl width w                 | 4 mm                     |
| Working range                     | 3 - 50 mm                |
| Cutting direction                 | left-hand and right-hand |
| for knurl profile                 | RAA 1×BR30°              |
| for knurl profile                 | RBL30° 1×AA              |
| for knurl profile                 | RAA 1×BL30°              |
| for knurl profile                 | RBL45° 1×BR15°           |
| for knurl profile                 | RBR45° 1×BL15°           |
| for knurl profile                 | RBR30° 1×AA              |

Type of product

Self-centring knurling tool