

Garant**Arbor for indexable drills, PSC 50 short, for shank Ø Ds: 16mm****Order data**

Order number	308584 16
GTIN	4067263141136
Item class	31A

Description**Version:**

- **Position of the grub screw for countersinking in the indexable drill offset by 0.4 mm.**
- **When tightening the increased contact face Ø is clamped against the front face of the arbor.**
- **Better support, allowing higher feed rates.**
- **High concentricity due to 3 µm ground flat contact face.**
- **With RFID/Balluffchip bore.**

Application:

For mounting all standard indexable drills to DIN 6595, Part 1.

Suitable for:

All indexable drills with parallel shank to DIN 6595, Part 1.

Optional extras:

Coolant tube No. 309885; socket No. 309893.

Technical description

External Ø D	36 mm
Overhang dimension A	65 mm
Adapter	PSC 50 short
Arbor standard	ISO 26623-1
Through-coolant	yes

Data sheet

Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 3 \mu\text{m}$
Machining strategy	HPC
Machining strategy	HSC
Type of product	Side lock arbor