



Holder for burnishing roller Fixed head, universal, Shank size: 16-25



Order data

Order number	291412 16-25
--------------	--------------

GTIN	
------	--

Item class	29M
------------	-----

Description

Version:

Fixed tool head (grub screw in the shank for clearance angle correction).

Advantage:

Surface quality of up to Rz 2 µm possible.

Application:

For machining materials up to 45 HRC. Ideal for machining the surfaces of complex, continuous contours.

For roller-burnishing of **uninterrupted contours** (convex, concave, cylindrical and conical).

Supplied with:

Shank size 16 including shank adaptor 20 mm × 20 mm and 25 mm × 25 mm.

Attention:

Burnishing rollers must be ordered separately!

Note:

For detailed application recommendations please see the instruction handbook supplied.

Check potential interference contours (x dimension of the roller = 2.5 mm).

Technical description

Product name attribute	universal
------------------------	-----------

Type of product

Smooth rolling tool