



Holder for burnishing roller Swivelling head, universal, Shank size: 16-25



Order data

Order number	291415 16-25
GTIN	4030741083037
Item class	29M

Description

Version:

Swivelling tool head (adjustment range $\pm 90^\circ$).

Advantage:

Surface quality of up to Rz 2 μm possible.

Application:

For machining materials up to 45 HRC. Ideal for machining the surfaces of complex, continuous contours.

For roller-burnishing of **uninterrupted contours** (convex, concave, cylindrical and conical) and flat faces. Suitable even for applications up to the collar.

Supplied with:

Shank size 16 including shank adaptor 20 mm $\times$ 20 mm and 25 mm $\times$ 25 mm.

Attention:

Burnishing rollers must be ordered separately!

Note:

For detailed application recommendations please see the instruction handbook supplied.
Check potential interference contours (x dimension of the roller = 2.5 mm).

Technical description

Data sheet

Product name attribute	universal
Type of product	Smooth rolling tool