

**Holder for burnishing roller Fixed head, universal, Shank size: 10-16****Order data**

Order number	291412 10-16
GTIN	4030741990816
Item class	29M

Description**Version:**

Fixed tool head (grub screw in the shank for clearance angle correction).

Advantage:

Surface quality of up to Rz 2 µm possible.

Application:

For machining materials up to 45 HRC. Ideal for machining the surfaces of complex, continuous contours.

For roller-burnishing of **uninterrupted contours** (convex, concave, cylindrical and conical).

Supplied with:

Shank size 10 including shank adaptor 12 mm × 12 mm and 16 mm × 16 mm.

Attention:

Burnishing rollers must be ordered separately!

Note:

For detailed application recommendations please see the instruction handbook supplied.
Check potential interference contours (x dimension of the roller = 2.5 mm).

Technical description

Product name attribute	universal
------------------------	-----------

Type of product

Smooth rolling tool