



Holder for burnishing roller Swivelling head, left-hand, Shank size: 10-16



Order data

Order number	291417 10-16
GTIN	
Item class	29M

Description

Version:

Swivelling tool head (adjustment range $\pm 90^\circ$).

Advantage:

Surface quality of up to Rz 2 μm possible.

Application:

For machining materials up to 45 HRC. Ideal for machining the surfaces of complex, continuous contours.

For roller-burnishing of **uninterrupted contours** (convex, concave, cylindrical and conical) and flat faces. Suitable even for applications up to the collar.

Supplied with:

Shank size 10 including shank adaptor 12 mm $\times$ 12 mm and 16 mm $\times$ 16 mm.

Attention:

Burnishing rollers must be ordered separately!

Note:

For detailed application recommendations please see the instruction handbook supplied. Check potential interference contours (x dimension of the roller = 2.5 mm).

Technical description

Product name attribute	left-hand
------------------------	-----------

Type of product

Smooth rolling tool