

Garant
Arbor 90°, cylindrical with IC long, Type: 20

Order data

Order number	239745 20
GTIN	4045197593269
Item class	23A

Description
Version:

Version suitable for NC with straight shank \varnothing for standard arbors especially in **hydraulic chucks** or **high precision collet chucks** for very high accuracy and process reliability.

Note:

Observe the mounting size of the holder and reaming heads. For further arbors see No. 210550 – 210582 and No. 212000.

Shank: DIN 6535 HA to h6

suitable for through hole \varnothing : 21.21 - 26.2 mm

suitable for blind hole \varnothing : 25.21 - 30.2 mm

Overall length L: 200 mm

Reach L_1 : 138 mm

Shank $\varnothing D_s$ h6: 25 mm

recommended tightening torque: 20 N·m

Technical description

suitable for blind hole \varnothing	25.21 - 30.2 mm
Shank $\varnothing D_s$ h6	25 mm
suitable for through hole \varnothing	21.21 - 26.2 mm
Reach L_1	138 mm
recommended tightening torque	20 N·m
Overall length L	200 mm
Series	TopCut

Through-coolant	yes
Shank	DIN 6535 HA to h6
Type of product	Threaded copy mill arbor