

**Holder M-Drill, Shank: MK3****Order data**

|              |               |
|--------------|---------------|
| Order number | 080750 MK3    |
| GTIN         | 4069515008587 |
| Item class   | BAW           |

**Description****Version:**

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

The M-Drill collet chucks are equipped with an aluminium cooling ring with bores to efficiently dissipate the heat generated during flow drilling. As a result, no heat is introduced into the machine spindle.

Standard or long; with or without a collar.

**Suitable for:**

HOLEX ER collets No. 308964.

ER clamping wrench No. 309680 25.

HOLEX fluteless tap No. 139130 or No. 139180.

**Technical description**

|                      |       |
|----------------------|-------|
| ER chuck key         | 25    |
| External Ø D         | 42 mm |
| Overhang dimension A | 80 mm |

## Data sheet

|                       |               |
|-----------------------|---------------|
| Spare ER clamping nut | 25            |
| for ER collets        | 25            |
| Clamping range        | 1 - 16 mm     |
| Type of product       | Collet chucks |