

**Flow drill - standard (with collar) Uni, Threads: M10****Order data**

Order number	080751 M10
GTIN	4069515008655
Item class	BAW

Description**Version:**

Very quickly produce core holes in thin-walled materials using frictional heat. Can be used on CNC, NC and pillar drilling machines.

Flow drill - standard (with collar).

Standard or long; with or without a collar.

Application:

Suitable for steel, stainless steel, aluminium, copper, brass.

Suitable for:

HOLEX ER collets No. 308964.

ER chuck key No. 309680.

HOLEX fluteless tap No. 139130 or No. 139180.

Technical description

Material thickness	0.7 - 2.5 mm
recommended drive power	1.7 kW
Shank Ø	10 mm

Data sheet

recommended speed	2100 min ⁻¹
Tapping hole Ø	9.2 mm
Type of product	Flow drill