



CNMG 120404, Grade: PR1325

Order data

Order number	250102 PR1325
GTIN	4960664627820
Item class	25E

Description

CNMG 120404 PR1325 Grade: PR1325
 Chip breaker: MQ
 Cutting depth a_p : 0.2 - 1.5 mm
 Feed f : 0.03 - 0.12 mm/rev.
 Cutting speed v_c main application: 40 - 100 m/min

Technical description

Indexable insert clearance angle	degrees
Product name attribute	
Insert assignment	
Rake	degrees
Shim	
Indexable insert profile	neutral
Type of product	